


# Installation Guide for UTPLinks Card CXM22 & CHM22

## IF USING CXM22 CARDS

The CXM22 card has four camera ports on the front of it. Connections for the camera ports are shown below in the chart labeled CAMERA PORT. All RJ45 jacks are wired to the T568B standard. Video from each of the four camera ports is routed to a single RJ45 jack on the rear of the CX452 unit. Each card has its own RJ45 jack and connections are shown in the chart below labeled VIDEO PORT. Using a standard RJ45 cable you can then route the video signals on the copper backbone of the facility. Control data for a PTZ can be connected using the 2 pin jack on the rear of the CX452.




## IF USING CHM22 CARDS

When using a CHM22 card the video for each camera is provided out the front of the card on BNC jacks. Connections for the camera port are shown above in the chart labeled CAMERA PORT. Video from the BNC can be fed into other equipment as needed. Control data for a PTZ can be connected to the 2 pin jack on the rear of the CX452.

## ADJUSTING CAMERA OUTPUT VOLTAGE (CHM22 & CXM22)

Camera output voltage can be adjusted by moving the voltage jumpers which are located in the middle of the circuit board. Three options are available: 28VAC, 24VAC, or no voltage output.



USA Office:  
5410 Newport Drive  
Rolling Meadows, IL 60008  
Phone: (800) 528-4343  
Fax: (847) 259-1300  
E-mail: [info@nitek.net](mailto:info@nitek.net)  
Web: [www.nitek.net](http://www.nitek.net)

**NITEK**<sup>®</sup>

European Office:  
De Schans 19-21 2a  
8231 KA Lelysted  
Netherlands  
Phone: +31(0)320 -230005  
Fax: +31(0)320 -230005  
E-mail: [info@nitek.nl](mailto:info@nitek.nl)  
Web: [www.nitek.nl](http://www.nitek.nl)